



CERTIFICATE NCS/FI 29436

Our Ref. 280487

Product	Range of enclosures	
Type	EURONORD PC EURONORD ABS	
Trade mark	FIBOX	
Certificate Holder/ Manufacturer	Fibox Oy Ab HTC Center Keilaranta 19 FI-02150 ESPOO FINLAND	
Technical information	Degree of protection (EN 60529)	IP66 / IP67
	Mechanical strength (EN 62262)	PC: IK08 (front surface) IK07 (side surface) ABS: IK07
	Static loads	mounting plate 1 kg/dm ² mounting rail 5 kg/rail
Other information	Material Polycarbonate (PC) / Acrylonitrile butadiene styrene (ABS) Empty enclosure Nominal voltage 1000 V AC and 1500 V DC The series includes the following types, see the Appendix to this Certificate	

The product is certified according to the following standard(s)
EN 62208:2011
EN 61439-1:2012

Validity This certificate is valid until 25 January 2021 unless the standard in question has been amended or superseded with significant changes in requirements, in which case, SGS Fimko has the right to shorten the validity of the certificate based on the legislation of the European Union. This certificate includes the right to use the FI mark under the condition that changes (if any) will be checked at SGS Fimko before the product is brought onto market and that the conditions for FI certification are met.

Directive information The product(s) fulfils the essential safety requirements for CE conformity marking according to the Low Voltage Directive (2006/95/EC) at the date of issue of the certificate.

Date of issue 25 January 2016

SGS Fimko Ltd

Signature

Sixten Lökfors
Project Manager



SGS
This certificate has 1 appendix



This certificate is issued by the company under its General Conditions for Certification Services accessible at <http://www.sgs.fi/en/Terms-and-Conditions.aspx>. Attention is drawn to the limitations of liability defined therein and in the Test Report here above mentioned which findings are reflected in this certificate. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law.

Manufacturing site(s) FiboxPAM Oy
 Rajasilta 6
 FI-33880 LEMPÄÄLÄ
 FINLAND

The series includes the following types



Type	Size (mm)
PC/AB 050504	52x50x40
PC/AB, PCT/ABT 050705	65x50x45
PC/AB, PCT/ABT, PCQ/ABQ, PCTQ/ABTQ 071004	98x66x41
PC/AB, PCT/ABT 080806	82x80x55
PC/AB, PCT/ABT 080807	82x80x65
PC/AB, PCT/ABT 080809	82x80x85
PC/AB, PCT/ABT 080810	82x80x95
PC/AB, PCT/ABT 081206	120x80x55
PC/AB, PCT/ABT 081206H	120x80x60
PC/AB, PCT/ABT 081209	120x80x85
PC/AB, PCT/ABT 081209H	120x80x90
PC/AB, PCT/ABT 081606	160x80x55
PC/AB, PCT/ABT 081607	160x80x65
PC/AB, PCT/ABT 081609	160x80x85
PC/AB, PCT/ABT 081610	160x80x95
PC/AB, PCT/ABT 121207	122x120x65
PC/AB, PCT/ABT 121208	122x120x75
PC/AB, PCT/ABT 121210	122x120x95
PC/AB, PCT/ABT 121211	122x120x105
PC/AB, PCT/ABT 121609	160x120x90
PC/AB, PCT/ABT 121614	160x120x140
PC/AB, PCT/ABT 122008	200x120x75
PC/AB, PCT/ABT 122009	200x120x90
PC/AB, PCT/ABT, PCQ(3)/ABQ(3), PCTQ(3)/ABTQ(3) 122410	244x124x102
PC/AB, PCT/ABT 152008	201x151x80
PC/AB, PCT/ABT, PCQ(3)/ABQ(3), PCTQ(3)/ABTQ(3) 153410	340x150x101
PC/AB, PCT/ABT, PCQ/ABQ, PCTQ/ABTQ 153412	340x150x121
PC/AB, PCT/ABT, PCQ(3)/ABQ(3), PCTQ(3)/ABTQ(3) 162409	244x164x90
PC/AB, PCT/ABT, PCQ/ABQ, PCTQ/ABTQ 162412	244x164x120
PC/AB, PCT/ABT 162509	250x160x90
PC/AB, PCT/ABT 162513	250x160x125
PC/AB, PCT/ABT 162515	250x160x150
PC/AB, PCT/ABT, PCQ(3)/ABQ(3), PCTQ(3)/ABTQ(3) 163610	360x160x101
PC/AB, PCT/ABT, PCQ(3)/ABQ(3), PCTQ(3)/ABTQ(3) 203615	360x200x151
PC/AB, PCT/ABT 233009	300x230x87
PC/AB, PCT/ABT, PCQ/ABQ, PCTQ/ABTQ 233011	300x230x110
ABQ3 364012	400x360x121
AB, ABQ 364015	400x360x151

PC/AB - grey PC/ABS cover
 PCT/ABT - clear PC cover
 Q - quick screw
 Q3 - new quick screw